

Hygizone Extraction Specification Sheet:

Product

HH100

Includes: 3 x various size flush-saddles for connection to cistern flush-pipe, 4m & 2m flexible hose (55mm diameter), 12VDC fan unit (110mm diameter) & power supply, exterior extraction grille.

Material info

All fittings: ABS

Hose: Polypropylene

Power Supply:

Input: 100-240VAC 50/60HZ 0.8A

Output: 12VDC, 1A



Fan:

DC 12V - 3.6W



Airflow:

2.6L/s @ -54Pa



Installation process:



Step 1. Install the cistern.



Step 2. Connect extraction hose.



Step 3. Route hose towards the ceiling.



Step 4. Install the fan in a suitable location.